



SKU
357000VA

Job Name:
Mark:
Submitted By:
Date: 08/02/2025

Motor, Large Frame, A44-3000-2112, 100 HP, 1200 RPM, 460V, 60HZ, 3PH, Product # 357000VA

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
100 HP	1200	460	60	3	115

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	No	Frame Size	444T
Frame Type	n/a	Housing Material	Cast Iron
Motor Enclosure	Totally Enclosed Air Over	Motor Insulation	H
Motor Phase	3	Motor Type	NEMA
Shipping Type	Freight		

Dimensions

Shaft Diameter	3.375 in	Weight	1800 lbs
-----------------------	----------	---------------	----------