


SKU SP-LP0511H Job Name: Mark: Submitted By: Date: 06/25/2025

# MultiSPEC SP-LP0511H Low-Profile Exhaust Fan with Humidity Sensor



- ENERGY STAR rated
- Virtually silent EC motor with 3 high speeds (50-80-110 CFM)
- Constant CFM technology
- 3-1/2 Inch Housing Depth the low profile is ideal for wall or ceiling installations. Easily fits in a 2x4 stud bay
- Integrated humidity sensor that helps control bathroom condensation to prevent mold and mildew
- 3-year warranty on EC motor and parts, excluding light
- UL listed for tub/shower enclosure when GFCI protected



#### Certifications

UL/cUL 507

Home Ventilating Institute (HVI)

#### **Performance Characteristics**

No Fan Curve Available.

#### **Construction Features**

Drive Type	Direct Drive			
Impeller Type	Centrifugal Wheel			
Impeller Material	Polypropylene			
Includes	Backdraft damper			
	Mounting brackets			
	UL/cUL 507			
Certifications	Home Ventilating Institute			
	(HVI)			
Speed Controllable	Yes			

#### **Motor Information**

Motor Phase	1
Voltage	115
Hertz	60
Watts	22.7

### Air and Sound Performance

Watts	Max Fan RPM	Min Fan RPM	Ps (in. wg)	0.1	0.25	0.4	0.5
13.5 752	752	CFM	50	50	50	50	
		Sones	>0.3	0.7	1.4	2.1	
18.5 838	838 CFM Sones	CFM	80	80	80	80	
		Sones	0.7	1.2	1.8	2.3	
22.7 1017	1017	CFM	110	110	110	110	
		Sones	1.5	2.1	2.2	2.3	

# California Residents



## **⚠** WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov