

SKU SP-LP0511HL Job Name: Mark: Submitted By: Date: 06/27/2025

MultiSPEC SP-LP0511HL Low-Profile Lighted Exhaust Fan with Humidity Sensor



- ENERGY STAR rated
- Virtually silent EC motor with 3 high speeds (50-80-110 CFM)
- Constant CFM technology
- 3-1/2 Inch Housing Depth the low profile is ideal for wall or ceiling installations. Easily fits in a 2x4 stud bay
- 10W dimmable LED chip panel, 750 lumens, 3000K warm white color temperature, and Rated Life of 50,000 hours
- Integrated humidity sensor that helps control bathroom condensation to prevent mold and mildew
- UL listed for tub/shower enclosure when GFCI protected
- 3-year warranty on EC motor and parts, excluding light

Certifications

UL/cUL 507 Home Ventilating Institute (HVI) ENERGY STAR® Certified

Performance Characteristics

No Fan Curve Available.

Construction Features

Watts

Drive Type	Direct Drive			
Impeller Type	Centrifugal Wheel			
Impeller Material	Polypropylene			
Includes	Backdraft damper Mounting brackets			
Certifications	UL/cUL 507 Home Ventilating Institute (HVI) ENERGY STAR® Certified			
Speed Controllable	Yes			
Motor Information				

Motor Phase 1 Voltage 115 Hertz 60

22.6

Air and Sound Performance

Watts	Max Fan RPM	Min Fan RPM	Ps (in. wg)	0.1	0.25	0.4	0.5
14.3 77	771	771 771	CFM	50	50	50	50
	//1		Sones	>0.3	0.7	1.4	2.1
18.5 871	071	871	CFM	80	80	80	80
	871		Sones	0.7	1.2	1.8	2.3
22.6	1063 1063	1000	CFM	110	110	110	110
		Sones	1.5	2.1	2.2	2.3	

California Residents



This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov