



SKU
1044247

Job Name:
Mark:
Submitted By:
Date: 08/18/2025

Motor, Large Frame, EM4104T-5-M25A, 30 HP, 1800 RPM, 575V, 60 Hz, 3 Phase,
Product # 1044247

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
30 HP	1800	575	60	3	29

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	No	Frame Size	286T
Frame Type	n/a	Housing Material	Cast Iron
Motor Enclosure	Totally Enclosed Fan Cooled	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
Shipping Type	Freight	Thermal Protection	Thermistors

Dimensions

Shaft Diameter	1.875 in	Weight	408 lbs
----------------	----------	--------	---------