



SKU  
358868

Job Name:  
Mark:  
Submitted By:  
Date: 06/21/2026

## Motor, 3GKP092540-ASK+461, 1.5 Kw, 3 Phase, Product # 358868

### Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
1.5 KW	1500	400	50	3	-

### Specifications

Base Type	Rigid Base	Country of Origin (Primary)	FI
Explosion Proof	n/a	Frame Size	90
Frame Type	M	Housing Material	NA
Motor Enclosure	n/a	Motor Insulation	F
Motor Phase	3	Motor Type	IEC
Return Eligibility	Non-returnable, customized, or special-order item	Shipping Type	Freight
Thermal Protection	Thermistors		

### Dimensions

Shaft Diameter	24 in	Weight	115 lbs
----------------	-------	--------	---------