



SKU
1059177

Job Name:
Mark:
Submitted By:
Date: 08/26/2025

Motor, Custom, 0.75 Kw, 1500 RPM, 280/400/415V, 50 Hz, 3 Phase, Product # 1059177

Performance Characteristics

Specifications

Base Type	C-Face Footless	Country of Origin (Primary)	US
Explosion Proof	n/a	Frame Size	80
Frame Type	NA	Housing Material	Cast Iron
Motor Enclosure	n/a	Motor Insulation	H
Motor Phase	3	Motor Type	IEC
Shipping Type	Freight		

Dimensions

Shaft Diameter	19 in	Weight	594 lbs
----------------	-------	--------	---------

California Residents

WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov