



SKU  
357074

Job Name:  
Mark:  
Submitted By:  
Date: 05/16/2026

## Motor, 36-0000-0422, 3 HP, 3 Phase, Product # 357074

### Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
3 HP	1800	460	60	3	4.2
3 HP	1800	230	60	3	8.4

### Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	Yes	Frame Size	182T
Frame Type	n/a	Housing Material	Rolled Steel
Motor Enclosure	Totally Enclosed Fan Cooled	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
Return Eligibility	Non-returnable, customized, or special-order item	Shipping Type	Freight
Thermal Protection	Thermostat		

### Dimensions

Shaft Diameter	1.125 in	Weight	102 lbs
----------------	----------	--------	---------