



SKU
1063557

Job Name:
Mark:
Submitted By:
Date: 06/08/2026

Motor, 56T11F5542, 0.75 HP, 3 Phase, Product # 1063557

Performance Characteristics

Specifications

Base Type	C-Face Footed	Country of Origin (Primary)	MX
Explosion Proof	No	Frame Size	56C
Frame Type	n/a	Hertz	60
Housing Material	Rolled Steel	HP	1/3
Motor Enclosure	Totally Enclosed Fan Cooled	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
NEMA Frame Size	48	Nominal Efficiency	64
Return Eligibility	Non-returnable, customized, or special-order item	RPM	1800
Service Factor	1.35	Shipping Type	Freight
Voltage	115 208 230		

Dimensions

Shaft Diameter	0.625 in	Weight	30 lbs
----------------	----------	--------	--------

California Residents

 **WARNING**

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov