



SKU
357365

Job Name:
Mark:
Submitted By:
Date: 05/08/2026

Motor, 00736ET3E213T-W22 Modified, 7.5 HP, 3 Phase, Product # 357365

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
7.5 HP	3600	460	60	3	8.76
7.5 HP	3600	230	60	3	17.5
7.5 HP	3600	208	60	3	19.4

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	BR
Explosion Proof	No	Frame Size	213T
Frame Type	n/a	Housing Material	Cast Iron
Motor Enclosure	Totally Enclosed Fan Cooled	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
Return Eligibility	Non-returnable, customized, or special-order item	Shipping Type	Freight

Dimensions

Shaft Diameter	1.375 in	Weight	157 lbs
-----------------------	----------	---------------	---------