



SKU  
357237

Job Name:  
Mark:  
Submitted By:  
Date: 08/31/2025

Motor, 05G808X014G1, 1 HP, 3 Phase, Product # 357237

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
1 HP	1800	460	60	3	1.5
1 HP	1800	230	60	3	3

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	Yes	Frame Size	143T
Frame Type	n/a	Housing Material	Cast Iron
Motor Enclosure	Totally Enclosed Fan Cooled	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
Shipping Type	Freight	Thermal Protection	Thermostat

Dimensions

Shaft Diameter	0.875 in	Weight	80 lbs
----------------	----------	--------	--------