



SKU
MV-750-VG-115

Job Name:
Mark:
Submitted By:
Date: 05/31/2025

Energy Recovery Ventilator, Product # MV-750-VG-115




The MiniVent is an energy recovery ventilator designed for indoor installations in commercial and institutional applications. The compact design provides an economical solution for individual spaces, such as school classrooms and small offices and may be floor mounted or ceiling hung. A removable panel enables easy access to filters and enthalpy wheel.

- Energy efficient, Vari-Green motor
- Total enthalpy wheel certified to AHRI Standard 1060
- Speed controllable with a motor potentiometer or a 0-10 VDC Signal

Certifications


UL 1812

AHRI 1060



A	B	C
43.2 in	33 in	23.8 in

Performance Characteristics



Construction Features

Housing Material	Galvanized Steel
Drive Type	Direct Drive
Impeller Type	Centrifugal Wheel
Includes	1 inch pleated filters
Certifications	UL 1812 AHRI 1060
Speed Controllable	Yes

Motor Information

Motor Insulation	B
Motor Phase	1
Motor Type	BrushlessDC
Service Factor	1
Voltage	115
HP	3/4
Hertz	60
RPM	1800
Thermal Protection	Auto
Nominal Efficiency	85

California Residents

WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov