



SKU
311812

Job Name:
Mark:
Submitted By:
Date: 04/10/2026

Vari-Green Motor - 1/2 HP, 115V, 1725RPM , Product # 311812

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.5 HP	1800	115	60	1	6.2
0.5 HP	1800	110	50	1	6.2

Specifications

Base Type	Extended Thru-Bolt Mount	Country of Origin (Primary)	US,MX
Explosion Proof	n/a	Frame Size	n/a
Frame Type	n/a	Hertz	60
Housing Material	NA	HP	1/2
Motor Enclosure	n/a	Motor Insulation	B
Motor Phase	1	Motor Type	BrushlessDC
NEMA Frame Size	48	Nominal Efficiency	85
Return Eligibility	Non-returnable, customized, or special-order item	RPM	1800
Service Factor	1	Shipping Type	Parcel
Thermal Protection	AutoOverload	Voltage	115

Dimensions

Weight 12 lbs

California Residents

 **WARNING**

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov