



SKU
313224

Job Name:
Mark:
Submitted By:
Date: 08/31/2025

Motor, S33G382YB-13, 0.0333 HP, 1050|1300|1550 RPM, 115V, 60 Hz, 1 Phase, Product # 313224



Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.033 HP	1050	115	60	1	0.68
0.033 HP	1300	115	60	1	1.1
0.033 HP	1550	115	60	1	1.1

Specifications

Base Type	Extended Thru-Bolt Mount	Country of Origin (Primary)	CN
Explosion Proof	n/a	Frame Size	n/a
Frame Type	n/a	Hertz	60
Housing Material	Rolled Steel	HP	1/30
Motor Enclosure	n/a	Motor Insulation	B
Motor Phase	1	Motor Type	Shaded Pole
Nominal Efficiency	25.5	RPM	1550
Service Factor	1	Shipping Type	Parcel
Thermal Protection	AutoOverload	Voltage	115

Dimensions

Height	10 in	Length	11 in
Weight	4 lbs	Width	11 in

California Residents

WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov