



SKU
312282

Job Name:
Mark:
Submitted By:
Date: 04/01/2026

Motor, YHS80-30-2.5uF, 20.4 Watts, 1100 RPM, 115V, 60Hz, 1Ph, Product # 312282

Performance Characteristics



Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
20.4 W	1100	115	60	1	0.2

Specifications

Base Type	Yoke Mount	Country of Origin (Primary)	CN
Explosion Proof	n/a	Frame Size	n/a
Frame Type	n/a	Hertz	60
Housing Material	Rolled Steel	Motor Enclosure	n/a
Motor Insulation	A	Motor Phase	1
Motor Type	PSC	Nominal Efficiency	30
Return Eligibility	Non-returnable, customized, or special-order item	RPM	1100
Service Factor	1	Shipping Type	Parcel
Thermal Protection	AutoOverload	Voltage	115
Watts	20.4		

Dimensions

Height	10 in	Length	11 in
Weight	3.062 lbs	Width	11 in

California Residents

⚠ WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov