

SKU
306329Job Name:
Mark:
Submitted By:
Date: 06/25/2025

Motor, 1.1Kw, 1000 RPM, 200/220/240/380/400/415V, 50Hz, 3Ph, Product # 306329

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
1.1 KW	1000	240	50	3	3.33
1.1 KW	1000	380	50	3	3.33
1.1 KW	1000	220	50	3	3.33
1.1 KW	1000	200	50	3	6.66
1.1 KW	1000	400	50	3	-
1.1 KW	1000	415	50	3	-

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	BR
Explosion Proof	n/a	Frame Size	90
Frame Type	L	Housing Material	NA
Motor Enclosure	n/a	Motor Insulation	H
Motor Phase	3	Motor Type	IEC
Shipping Type	Parcel		

Dimensions

Shaft Diameter	24 in	Weight	43 lbs
----------------	-------	--------	--------

California Residents

WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov