



SKU
302059

Job Name:
Mark:
Submitted By:
Date: 04/03/2026

Motor, EM3218T, 5 HP, 3 Phase, Product # 302059



Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
5 HP	1800	460	60	3	6.6
5 HP	1800	230	60	3	13.2
5 HP	1800	208	60	3	14

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	No	Frame Size	184T
Frame Type	n/a	Hertz	60
Housing Material	Rolled Steel	HP	5
Motor Enclosure	Open Drip Proof	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
NEMA Frame Size	184T	Nominal Efficiency	89.5
Return Eligibility	Returnable within 60 days of shipment	RPM	1800
Service Factor	1.15	Shipping Type	Freight
Voltage	208-230/460		

Dimensions

Height	13 in	Length	19 in
Shaft Diameter	1.125 in	Weight	83 lbs
Width	14 in		

California Residents

⚠ WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov