

SKU
302059Job Name:
Mark:
Submitted By:
Date: 09/23/2025**Motor, EM3218T, 5 HP, 1800 RPM, 208/230/460V, 60 Hz, 3 Phase, Product # 302059****Performance Characteristics**

| Power | Speed | Voltage | Frequency | Phase | Full Load Amp Draw |
|-------|-------|---------|-----------|-------|--------------------|
| 5 HP | 1800 | 460 | 60 | 3 | 6.6 |
| 5 HP | 1800 | 208 | 60 | 3 | 14 |
| 5 HP | 1800 | 230 | 60 | 3 | 13.2 |

Specifications

| | | | |
|------------------|-----------------|-----------------------------|-------------|
| Base Type | Rigid Base | Country of Origin (Primary) | US |
| Explosion Proof | No | Frame Size | 184T |
| Frame Type | n/a | Hertz | 60 |
| Housing Material | Rolled Steel | HP | 5 |
| Motor Enclosure | Open Drip Proof | Motor Insulation | F |
| Motor Phase | 3 | Motor Type | NEMA |
| NEMA Frame Size | 184T | Nominal Efficiency | 89.5 |
| RPM | 1800 | Service Factor | 1.15 |
| Shipping Type | Freight | Voltage | 208-230/460 |

Dimensions

| | | | |
|----------------|----------|--------|--------|
| Height | 13 in | Length | 19 in |
| Shaft Diameter | 1.125 in | Weight | 84 lbs |
| Width | 14 in | | |

California Residents**⚠ WARNING**

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov