



SKU  
300208

Job Name:  
Mark:  
Submitted By:  
Date: 04/05/2026

## Motor, 048S17D2058-R, 0.5 HP, 1 Phase, Product # 300208



### Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.5 HP	1800	115	60	1	7.5

### Specifications

Base Type	Resilient Base	Country of Origin (Primary)	MX
Explosion Proof	No	Frame Size	48
Frame Type	n/a	Hertz	60
Housing Material	Rolled Steel	HP	1/2
Motor Enclosure	Open Drip Proof	Motor Insulation	B
Motor Phase	1	Motor Type	NEMA
NEMA Frame Size	48	Nominal Efficiency	69.5
Return Eligibility	Non-returnable, customized, or special-order item	RPM	1800
Service Factor	1.25	Shipping Type	Parcel
Voltage	115		

### Dimensions

Height	6 in	Length	10 in
Shaft Diameter	0.5 in	Weight	18 lbs
Width	6 in		

### California Residents

**⚠ WARNING**

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)