

SKU
310109Job Name:
Mark:
Submitted By:
Date: 12/14/2025

Motor, M3534, 0.333 HP, 3 Phase, Product # 310109

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.333 HP	1800	208	60	3	1.3
0.333 HP	1800	460	60	3	0.7
0.333 HP	1800	230	60	3	1.4

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	No	Frame Size	56
Frame Type	n/a	Hertz	60
Housing Material	NA	HP	1/3
Motor Enclosure	Totally Enclosed Fan Cooled	Motor Insulation	B
Motor Phase	3	Motor Type	NEMA
NEMA Frame Size	56	Nominal Efficiency	68
Return Eligibility	Non-returnable, customized, or special-order item	RPM	1800
Service Factor	1.35	Shipping Type	Parcel
Voltage	208-230/460		

Dimensions

Shaft Diameter	0.625 in	Weight	21 lbs
----------------	----------	--------	--------

California Residents

WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov