



SKU  
356790

Job Name:  
Mark:  
Submitted By:  
Date: 06/21/2026

---

## Vari-Green Motor, EC Titanium Motor with Integrated Drive, ECS101A4H2DF4, 2 HP, 1800 RPM, 380/460V, 60 Hz, 3 Phase, Product # 356790

---

### Performance Characteristics

---

#### Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	n/a	Frame Size	n/a
Frame Type	n/a	Housing Material	Rolled Steel
Motor Enclosure	n/a	Motor Insulation	F
Motor Phase	3	Motor Type	Synchronous Reluctance
Return Eligibility	Returnable within 60 days of shipment	Shipping Type	Parcel
Thermal Protection	AutoOverload		

#### Dimensions

---

Weight	42 lbs
--------	--------