



SKU  
311717

Job Name:  
Mark:  
Submitted By:  
Date: 07/05/2025

## Motor, M1718, 0.2|0.5HP, 1200|1800 RPM, 460V, 60Hz, 3Ph, Product # 311717

### Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.2 HP	1200	460	60	3	0.69
0.5 HP	1800	460	60	3	1.1

### Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	No	Frame Size	56
Frame Type	n/a	Housing Material	NA
Motor Enclosure	Totally Enclosed Fan Cooled	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
Shipping Type	Parcel		

### Dimensions

Shaft Diameter	0.625 in	Weight	29 lbs
----------------	----------	--------	--------

### California Residents

#### WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)