




SKU  
328174

Job Name:  
Mark:  
Submitted By:  
Date: 05/18/2026

# Vari-Green Motor, Pre-Programmed, FA520A4730, 0.29 HP, 1 Phase, Product # 328174

## Performance Characteristics



Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.29 HP	1550	277	50	1	2.2
0.29 HP	1550	115	50	1	4.1
0.29 HP	1550	230	60	1	2.4
0.29 HP	1550	220	50	1	2.4
0.29 HP	1550	110	50	1	4.1
0.29 HP	1550	240	60	1	2.4
0.29 HP	1550	230	50	1	2.4
0.29 HP	1550	240	50	1	2.4
0.29 HP	1550	220	60	1	2.4
0.29 HP	1550	208	50	1	2.4
0.29 HP	1550	115	60	1	4.1
0.29 HP	1550	277	60	1	2.2
0.29 HP	1550	208	60	1	2.4

## Specifications

Base Type	Resilient Base	Country of Origin (Primary)	MX,US
Explosion Proof	n/a	Frame Size	n/a
Frame Type	n/a	Housing Material	Rolled Steel
Motor Enclosure	n/a	Motor Insulation	B
Motor Phase	1	Motor Type	BrushlessDC
Return Eligibility	Returnable within 60 days of shipment	Shipping Type	Parcel
Thermal Protection	OneShot		

## Dimensions

Weight 0 lbs

## California Residents

**⚠ WARNING**

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)