



SKU  
304387

Job Name:  
Mark:  
Submitted By:  
Date: 06/03/2026

## Motor, 0.25HP, 1800 RPM, 115V, 60Hz, 1Ph, Product # 304387

### Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.25 HP	1800	115	60	1	4.1

### Specifications

<b>Base Type</b>	Resilient Base	<b>Country of Origin (Primary)</b>	TH
<b>Explosion Proof</b>	No	<b>Frame Size</b>	48
<b>Frame Type</b>	n/a	<b>Housing Material</b>	NA
<b>Motor Enclosure</b>	Open Drip Proof	<b>Motor Insulation</b>	B
<b>Motor Phase</b>	1	<b>Motor Type</b>	NEMA
<b>Return Eligibility</b>	Non-returnable, customized, or special-order item	<b>Shipping Type</b>	Parcel
<b>Thermal Protection</b>	AutoOverload		

### Dimensions

<b>Shaft Diameter</b>	0.5 in	<b>Weight</b>	17.5 lbs
-----------------------	--------	---------------	----------

### California Residents

 **WARNING**

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)