

SKU SP-A200-QD Job Name: Mark: Submitted By: Date: 08/17/2025


Bathroom Exhaust Fan, Product # SP-A200-QD, 68-267 CFM




- ENERGY STAR rated
- Acoustic insulation absorbs sound ensuring quiet operation
- Spring loaded aluminum backdraft damper eliminates rattling
- External electrical access reduces installation time
- Speed controllable
- Designer grille included

Certifications

AMCA Air & Sound UL/cUL 507



Performance Characteristics



Construction Features

Housing Material	Galvanized Steel				
Drive Type	Direct Drive				
Impeller Type	Centrifugal Wheel				
Impeller Material	Polypropylene				
Includes	Backdraft damper Mounting brackets				
Certifications	AMCA Air & Sound UL/cUL 507				
Speed Controllable	Yes				

Motor Information

Motor Insulation	В					
Motor Phase	1					
Motor Type	Shaded Pole					
Service Factor	1					
Voltage	115					
Hertz	60					
Motor Enclosure	n/a					
RPM	900					
Thermal Protection	AutoOverload					
Nominal Efficiency	29					
Watts	16.4					

Air and Sound Performance

	Watts	Max Fan RPM	Min Fan RPM	Ps (in. wg)	0	0.125	0.25	0.375	0.5	0.625	0.75
	00.4	000	700	CFM	267	242	224	199	162	109	68
26.1	900	720	Sones	2	2	2.5	3	3.5	4	4.5	



- Greenheck Fan Corporation certifies that the SP models shown herein are licensed to bear the AMCA seal.
- The ratings shown are based on tests and procedures performed in accordance with AMCA Publication 211 and AMCA Publication 311 and comply with the requirements of the AMCA Certified Ratings Program.
- The SP models are not AMCA certified with 50 hertz motors.

California Residents



⚠ WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov