



SKU
1002284

Job Name:
Mark:
Submitted By:
Date: 08/14/2025

Motor, Large Frame, EM2534T, 30 HP, 3600 RPM, 208-230/460V, 60 Hz, 3 Phase, Product # 1002284

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
30 HP	3600	230	60	3	70
30 HP	3600	208	60	3	76
30 HP	3600	460	60	3	35

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	No	Frame Size	284TS
Frame Type	n/a	Housing Material	Rolled Steel
Motor Enclosure	Open Drip Proof	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
Shipping Type	Freight		

Dimensions

Shaft Diameter	1.625 in	Weight	308 lbs
----------------	----------	--------	---------

California Residents

WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov