



SKU
314718VA

Job Name:
Mark:
Submitted By:
Date: 07/25/2025

Motor, 286T, 286Tttna16102, Product # 314718VA

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
15 HP	900	460	60	3	22

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	No	Frame Size	286T
Frame Type	n/a	Housing Material	Cast Iron
Motor Enclosure	Totally Enclosed Air Over	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
Shipping Type	Freight		

Dimensions

Shaft Diameter	1.875 in	Weight	421 lbs
-----------------------	----------	---------------	---------