

SKU SP-B150-QD Job Name: Mark: Submitted By: Date: 10/28/2025

Bathroom Exhaust Fan, Product # SP-B150-QD, 92-160 CFM




Low profile bathroom exhaust fan, Model SP-B features a forward-curved wheel for low sound and high efficiency. Units are ideal for residential, multifamily or hotel applications.


- Compact size for height restricted areas
- Round standard outlet for quick, easy connections
- Integral damper prevents unwanted backdrafts
- Speed controllable
- Designer grille included

Certifications

AMCA Air & Sound UL/cUL 507



Performance Characteristics



Construction Features

Housing Material	Galvanized Steel					
Drive Type	Direct Drive					
Impeller Type	Centrifugal Wheel					
Impeller Material	Polypropylene					
Includes	Backdraft damper Mounting brackets					
Certifications	AMCA Air & Sound UL/cUL 507					
Speed Controllable	Yes					

Motor Information

Motor Insulation	В					
Motor Phase	1					
Motor Type	Shaded Pole					
Service Factor	1					
Voltage	115					
Hertz	60					
Motor Enclosure	n/a					
RPM	1050					
Thermal Protection	AutoOverload					
Nominal Efficiency	15					
Watts	19.2					

Air and Sound Performance

Watts	Max Fan RPM	Min Fan RPM	Ps (in. wg)	0	0.125	0.25	0.375	0.5	0.625	0.75	0.875	1
128 1050	840	CFM	160	155	154	152	149	147	138	123	92	
		Sones	2.5	2.5	3	3.5	3.5	4	4.5	4.5	5	



- Greenheck Fan Corporation certifies that the SP models shown herein are licensed to bear the AMCA seal.
- The ratings shown are based on tests and procedures performed in accordance with AMCA Publication 211 and AMCA Publication 311 and comply with the requirements of the AMCA Certified Ratings Program.
- The SP models are not AMCA certified with 50 hertz motors.

California Residents



⚠ WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov