



SKU
312939

Job Name:
Mark:
Submitted By:
Date: 06/17/2025

Motor, 56H11O15503, 0.75|1.0HP, 1000|1200 RPM, 190/380//208-230/460V, 50/60Hz, 3Ph, Product # 312939



Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.75 HP	1000	380	50	3	2
1 HP	1200	230	60	3	4.2
1 HP	1200	460	60	3	2.1
0.75 HP	1000	190	50	3	4
1 HP	1200	208	60	3	4

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	MX
Explosion Proof	No	Frame Size	56
Frame Type	n/a	Housing Material	Rolled Steel
Motor Enclosure	Open Drip Proof	Motor Insulation	B
Motor Phase	3	Motor Type	NEMA
Shipping Type	Parcel		

Dimensions

Height	9 in	Length	27 in
Shaft Diameter	0.625 in	Weight	29 lbs
Width	9 in		

California Residents

WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov