



SKU
311103

Job Name:
Mark:
Submitted By:
Date: 08/09/2025

Motor, EM3211T-G, 3HP, 1800 RPM, 208-230/460V, 60Hz, 3Ph, Product # 311103



Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
3 HP	1800	208	60	3	8.5
3 HP	1800	460	60	3	4.2
3 HP	1800	230	60	3	8.4

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	No	Frame Size	182T
Frame Type	n/a	Housing Material	NA
Motor Enclosure	Open Drip Proof	Motor Insulation	H
Motor Phase	3	Motor Type	NEMA
Shipping Type	Freight		

Dimensions

Height	13 in	Length	19 in
Shaft Diameter	1.125 in	Weight	72 lbs
Width	14 in		

California Residents

WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov