



SKU SP-L80-QD Job Name: Mark: Submitted By: Date: 09/04/2025

Low Profile Bathroom Exhaust Fan, Product # SP-L80-QD, 33-86 CFM




Model SP-L, bathroom exhaust fan is a low profile, direct drive exhaust fan designed to fit in a 2x4 studded wall. Unit offers industry leading low sound levels and is ENERGY STAR® rated. • ENERGY STAR rated

- Low profile fits into a 2x4 studded wall
- White designer non-yellowing grille
- Plug type disconnect
- Corrosion resistant galvanized steel scroll and housing
- Designer grille included

Certifications

AMCA Air & Sound UL/cUL 507



Performance Characteristics

No Fan Curve Available.

Construction Features

Housing Material	Galvanized Steel			
Drive Type	Direct Drive			
Impeller Type	Centrifugal Wheel			
Impeller Material	Polypropylene			
Includes	Backdraft damper Mounting brackets			
Certifications	AMCA Air & Sound UL/cUL 507			
Speed Controllable	Yes			

Motor Information

Motor Insulation	A
Motor Phase	1
Motor Type	PSC
Voltage	115
Hertz	60
Motor Enclosure	n/a
RPM	850
Thermal Protection	AutoOverload
Watts	8

Air and Sound Performance

Watts	Max Fan RPM	Min Fan RPM	Ps (in. wg)	0	0.125	0.25	0.375	0.5	0.625
26.8	050	680	CFM	86	76	67	57	46	33
	850		Sones	1.5	2	2	2.5	3.5	4



- Greenheck Fan Corporation certifies that the SP models shown herein are licensed to bear the AMCA seal.
- The ratings shown are based on tests and procedures performed in accordance with AMCA Publication 211 and AMCA Publication 311 and comply with the requirements of the AMCA Certified Ratings Program.

The SP models are not AMCA certified with 50 hertz motors.

California Residents



This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov