



SKU  
312239

Job Name:  
Mark:  
Submitted By:  
Date: 06/13/2026

## Motor, Large Frame, 09P011Z509G1, 15 HP, 3 Phase, Product # 312239

### Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
15 HP	1800	380	60	3	21.4
15 HP	1800	190	60	3	42.8
15 HP	1800	400	60	3	21.3

### Specifications

<b>Base Type</b>	Rigid Base	<b>Country of Origin (Primary)</b>	US
<b>Explosion Proof</b>	No	<b>Frame Size</b>	254T
<b>Frame Type</b>	n/a	<b>Housing Material</b>	NA
<b>Motor Enclosure</b>	Totally Enclosed Fan Cooled	<b>Motor Insulation</b>	F
<b>Motor Phase</b>	3	<b>Motor Type</b>	NEMA
<b>Return Eligibility</b>	Non-returnable, customized, or special-order item	<b>Shipping Type</b>	Freight

### Dimensions

<b>Shaft Diameter</b>	1.625 in	<b>Weight</b>	255 lbs
-----------------------	----------	---------------	---------

### California Residents

 **WARNING**

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)