This cut sheet was generated from Greenheck Shop Online and is for the product SKU referenced below. Cut sheets for accessories or ancillary products must be printed separate



SKU SQ-95-DGEX-QD Job Name: Mark: Submitted By: Date: 07/16/2025

Centrifugal Inline Fan, Product # SQ-95-DGEX-QD, 275-920 CFM



Model SQ, direct drive centrifugal inline fans feature a unique combination of installation flexibility, rugged construction, ease of service, high efficiency and low sound levels. These compact fans are ideal for indoor clean air applications including exhaust, return or make-up where space is a prime consideration.

- Compact size for height-restricted areas
- Composite backward inclined, non-overloading centrifugal wheel design
- Inlet and discharge duct collars for easy duct connection
- Removable access panels permit easy access to interior components for cleaning and servicing.

Certifications

AMCA Sound & Air Performance UL/cUL 705



Performance Characteristics



Construction Features

Housing Material	Galvanized Steel				
Drive Type	Direct Drive				
Impeller Type	Centrifugal Wheel				
Impeller Material	Aluminum				
Includes	Access Panel Disconnect switch				
Certifications	AMCA Sound & Air Performance UL/cUL 705				
Speed Controllable	Yes				

Motor Information

Motor Insulation	В
Motor Phase	1
Motor Type	PSC
Service Factor	1
Voltage	115
HP	1/8
Hertz	60
Motor Enclosure	n/a
RPM	1550
Thermal Protection	AutoOverload
Nominal Efficiency	48
Watts	92.6

Air and Sound Performance

Motor HP	Max BHP	Max Fan RPM	Min Fan RPM	Ps (in. wg)	0	0.125	0.25	0.375	0.5	0.625
1/8 0.03	0.00	0.03 1050	0	CFM	623	475	275	-	-	-
	0.03			Sones	4.9	4.5	4.5	-	-	-
1/8 0.06	0.00	0.06 1300	0	CFM	771	660	523	352	-	-
	0.06			Sones	7.6	6.7	6.4	6.4	-	-
1/8	0.10	1550	0	CFM	920	830	720	604	462	276
				Sones	9.6	9.3	8.7	8.1	8.1	8.1



- Greenheck Fan Corporation certifies that the model shown herein is licensed to bear the AMCA Seal. The ratings shown are based on tests and procedures performed in accordance with AMCA Publication 211 and AMCA Publication 311 and comply with the requirements of the AMCA Certified Ratings Program.
- Performance certified is for installation type B: Free inlet, Ducted outlet.
- Power rating (BHP/kW) does not include transmission losses.
- Performance ratings do not include the effects of appurtenances (accessories).
- The inlet sound ratings shown are loudness values in fan sones at 5 ft. (1.5 m) in a hemispherical free field calculated per AMCA Standard 301. Values shown are for installation type B: free inlet hemispherical sone levels.

California Residents

▲ WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov