




SKU
311559

Job Name:
Mark:
Submitted By:
Date: 06/07/2025

Motor, D0810B4076, 19.5 Watts, 1400 RPM, 115V, 60Hz, 1Ph, Product # 311559



Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
19.5 W	1400	115	60	1	0.45

Specifications

Base Type	Extended Thru-Bolt Mount	Country of Origin (Primary)	US
Explosion Proof	n/a	Frame Size	n/a
Frame Type	n/a	Hertz	60
Housing Material	Rolled Steel	Motor Enclosure	n/a
Motor Insulation	B	Motor Phase	1
Motor Type	PSC	Nominal Efficiency	38
RPM	1400	Service Factor	1
Shipping Type	Parcel	Thermal Protection	AutoOverload
Voltage	115	Watts	19.5

Dimensions

Height	10 in	Length	11 in
Weight	5 lbs	Width	11 in

California Residents

WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov