



SKU
312028VA

Job Name:
Mark:
Submitted By:
Date: 07/21/2025

Motor, 145T, 145Ttn16035, Product # 312028VA

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
1.5 HP	1800	460	60	3	2.3

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	No	Frame Size	145T
Frame Type	n/a	Housing Material	Cast Iron
Motor Enclosure	Totally Enclosed Air Over	Motor Insulation	H
Motor Phase	3	Motor Type	NEMA
Shipping Type	Parcel		

Dimensions

Shaft Diameter	0.875 in	Weight	62 lbs
----------------	----------	--------	--------